

# **Technical Data Sheet**

Pressure / Temperature / Humidity / Air Velocity / Airflow / Sound level

# Vane probe thermo-anemometer LV 110 - LV 111 - LV 117

# **KEY POINTS**

- Airflow calculation

- Hold-min-max function

- Automatic average - Selection of units

# TECHNICAL FEATURES

Measuring elements	Air velocity : Hall effect sensor Ambient temperature : NTC sensor		
Display	4 lines, LCD technology. Sizes 50 x 36 mm 2 lines of 5 digits with 7 segments (value) 2 lines de 5 digits with 16 segments (unit)		
Vane probe diameter	LV111: Ø 14 mm / LV117: Ø 70 mm / LV110: Ø 100 mm		
Cable	Coiled, Ig. 0.45 m, extension : 2.4 m		
Housing	ABS, protection IP54		
Keypad	5 keys		
European directives	2014/30/EU EMC ; 2014/35/EU Low Voltage ; 2011/65/EU RoHS II ; 2012/19/EU WEEE		
Power supply	4 batteries AAA LR03 1.5 V		
Battery life	120 hours		
Ambience	Neutral gas		
Conditions of use (instrument) (°C, %RH, m)	From 0 to +50 °C. In non condensing conditions. From 0 to 2000 m.		
Operating temperature (probe)	From 0 to +50 °C		
Storage temperature	From -20 to +80 °C		
Auto shut-off	Adjustable from 0 to 120 min		
Weight	390 g		

#### **SPECIFICATIONS**

SPECII ICATIONS					
Models	Measuring units	Measuring range	Accuracy <sup>1</sup>	Resolution	
Air velocity					
LV111 : Ø 14 mm	m/s, fpm, km/h	From 0.8 to 25 m/s	From 0.8 to 3 m/s : ±3% of reading ±0.1 m/s From 3.1 to 25 m/s : ±1% of reading ±0.3 m/s	0.1 m/s	
LV110 : Ø 100 mm	m/s, fpm, km/h	From 0.3 to 35 m/s	From 0.3 to 3 m/s : $\pm 3\%$ of reading $\pm 0.1$ m/s From 3.1 to 35 m/s : $\pm 1\%$ of reading $\pm 0.3$ m/s	0.01 m/s 0.1 m/s	
LV117 : Ø 70 mm	m/s, fpm, km/h	From 0.4 0 to 35 m/s	From 0.4 to 3 m/s : ±3% of reading ±0.1 m/s From 3.1 to 35 m/s : ±1% of reading ±0.3 m/s	0.1 m/s	
Airflow					
All models	m³/h, cfm, l/s, m³/s	From 0 to 99 999 m³/h	±3% of reading ±0.03 * area (cm²)	1 m³/h	
Temperature					
All models	°C, °F	From -20 to +80 °C	±0.4 % of reading ±0.3 °C	0.1 °C	



Ø70 mm vane probe

Ø14 mm vane probe


#### **FUNCTIONS**

- Airflow calculation
- Airflow calculation with cone (LV 110/117)
- Automatic average
- Selection of units (air velocity, airflow and temperature)
- Hold function
- Display of minimum and maximum values
- Configurable auto shut-off
- Backlight
- Detection of flow direction (LV 110/117)
- Selection of the type of cone
- Dimensions of rectangular and circular duct

# OPERATING PRINCIPLES

#### Air velocity: Hall effect sensor

Rotation of the vane probe leads to a circular magnet of 8 poles. A dual Hall effect sensor, placed next to the magnet captures the signals of magnetic field polarity transition. The sensor signal is converted to electrical frequency and is proportional to the rotation velocity of the vane probe. Signal chronology allows to determine the rotation direction.



Frequency = vane velocity

#### Thermometer: CTN probe

Negative temperature coefficient probes are thermistors with a resistance that decreases with temperature according to the equation below:

$$\mathsf{R}_{(T)} \! = \! \mathsf{R}_{(T0)} \! \mathsf{e}^{-(\frac{\alpha}{100}\,\mathsf{x}\,(\mathsf{T}_{_{\!0}} \!+ 273.15)^2\,\mathsf{x}\,(\frac{1}{\mathsf{T} + 273.5} - \frac{1}{\mathsf{T}_{_{\!0}} + 273.5}\,))$$

RT= resistance sensor value at temperature T

R(T0)=resistance sensor value at reference temperature  $T_0$ 

 $\rm T$  and  $\rm T_{\scriptscriptstyle 0}\,$  in  $^{\circ}\rm C$ 

 $\alpha$  and  $T_0$  sensor specific constants

# SUPPLIED WITH

Instruments are supplied with:

- LV 111 : vane probe Ø 14 mm
- LV 117 : vane probe Ø 70 mm
- LV 110 : vane probe Ø 100 mm
- Calibration certificate\*
- Transport case (ref : ST 110)



\*Except class 110 S

# ACCESSORIES

**CQ 15**: Magnetic protective housing



RTE: Telescopic extension, length 1m, with index at ±90°

**K 25 – 85**: Airflow cones for anemometer LV 110



MT 51 : ABS transport case



# **MAINTENANCE**

We carry out calibration, adjustment and maintenance of your instruments to guarantee a constant level of quality of your measurements. As part of Quality Assurance Standards, we recommend you to carry out a yearly checking.

# **GUARANTEE**

Instruments have 1-year guarantee for any manufacturing defect (return to our After-Sales Service required for appraisal).

Distributed by: