

Embedded in the device to create the system



Connected to the PC for measuring with the GL7000 (no display module)

## Suitable for a variety of measurements due to flexible module combinations



released sequential

starting in the autumn of 2012

## oltage Module

 The output of various sensors such as displacement, pressure, wind speed, etc. Cell voltage of the battery.



## oltage/Temperature Module

 Measuring temperature and voltage simultaneously. For environmental tests, etc.



## ligh Speed Voltage Module

 Measurement of parameters in the inverter system, vibration test, drop test



## Logic/Pulse Module

 Timing of system control signal, encoder output, rotational speed, flow rate, etc.



## High Voltage Module

 Measurement of the high voltage in the power line of equipment, Electric or Hybrid Vehicle testing, etc.



 An analog voltage corresponding to the captured data is output. Simulation testing by the actual ured data, the vibration test, etc.



 Measuring the output of sensor using the strain gauge. asurement of the load, displacement, vibration acceleration, torque, pressure, etc.




 Measuring the output of sensor using the Piezoelectric device. Measurement of the vibration, acceleration, pressure, force, etc.



## Power Measurement Module

• Measuring the voltage, current and power. Measurement of the power line of the device, etc.



Weight					
		Main module: Approx. 2 kg, Alarm output terminal: Approx. 350 g			
Software sp	ecifications				
Model nam	e	GL-Connection			
Supported	os	Windows 7 (32/64-bits, Except Starter edition), Vista (32/64-bits), XP *13			
Functions		Control GL7000, Real-time data capture, Replay data, Data format conversion			
Controlled (	units	Up to 10 units (Max. 1120 channels)			
	ttings control	Input settings, Memory settings, Trigger and Alarm settings, Other settings			
Captued da	ta *14	Built-in RAM (Binary format), Built-in Flash memory (Binary, CSV format), SD memory card (Binary, CSV format), SSD (Binary, CSV format)			
		The sampling is limited by the number of channels used. (1 ms per channel.			
		When 10 channels are set, sampling is limited to 10 ms.)			
Displayed in	nformation	Analog waveforms, Logic waveforms, Pulse waveforms, Digital values			
Display mode		Y-T waveform with digital values, X-Y graph in real time, Cursor information, Capture condition, Alarm information			
File operation		Converts binary data to the CSV data (specific period, all data in one file, mulfiles), Creates a new file with compression or by consolidating multiple files.			
Warning Function		Send e-mail to the specified address when the alarms occur			
Statistical calculation		Capturing data: Maximum, Minimum, Peak or Average			
		Replaying data: Maximum, Minimum, Peak, Average or RMS in between curs			
Search	Level	Specific level in any channels			
function	Alarm	Occurred alarm in any channel			
	Time	Beginning, center, end of the data, Trigger point, Specific time (absolute, relative), Specific number			
Operation I	ock	Operation screen can be locked (It is unlocked with a password.)			

| S.7-inch TFT color LCD monitor (VGA: 640 x 480 dots)
| Touch panel and Cursor keys \*15 |
| Capacitive type touch panel, Operated by finger or the proprietary pen |
| English, French, German, Chinese, Korean, Japanese |
| Turns off backlight by 10, 30 sec., 1, 2, 5, 10, 30, 60 min. |
| Waveform in Y-T with digital values, Waveform only, Digital value, Waveform in X-Y |
| AN cable (CATS classes, Straight connection, Light of 10%) \*16. peration section Displayed information Waveform in Y-1 with digital values, Waveform only, Digital value, Waveform in X-1 Connection cable LAN cable (CAT5 class, Straight connection, Up to 10m) \*16 Standard accessories Bracket for slanted mount, Connection cable (40cm), Ground cable, Screws External dimensions (WkDxH) Approx. 187 x 35 x 199 mm (Excluding projection)

Weight Approx. 530 g

> | Solid state disk (SSD), Form factor: 2.5-inch HDI Approx. 64 GB (The file size of the captured data is limited up to 2 GB.)
>
> Attached to 1 Max. 1 M Samples/s

or 10 modules		
External dimensions (WxDxH)	Approx. 49 x 1	36 x 160 mm (Excluding projection)
Weight	Approx. 770 g	
Options and accessories		
Item	Model number	Remarks
Input/Output cable	B-513	2m, One end is bare wire
Humidity sensor	B-530	3m cables for signal and power
Sync. cable	B-559	1 m, Synchronizing between GL7000
	RIC-10	4 channels, Cable with Alligator clip and IC clip
Input cable, BNC - BNC	RIC-112	1.5m, Non-isolated, Max. 500V
Input cable, Banana - BNC	RIC-113	1.5m, Non-isolated, Max. 500V
Input cable, Banana - BNC	RIC-114	1.5m, Non-isolated, Max. 500V
Input cable, BNC - BNC	RIC-142	1.5m, Isolated, CAT II, Max. 1000V
Input cable, Banana - BNC	RIC-143	1.5m, Isolated, CAT II, Max. 600V
	RIC-144	CAT II, Max. 300V/15A, using with RIC-143
Clip, Alligator (middle size)	RIC-145	CAT II, Max. 1000V/32A, using with RIC-143
Clip, Grabber	RIC-146	CAT II, Max. 1000V/1A, using with RIC-143

or 2 modules

Attached to 3 Max. 500 k Samples/s

or 4 modules
Attached to 5 Max. 200 k Samples/s

- oues.

  1. Excluding the function module as the Display module or SSD module.

  2. The Input/Output cable (B-513) is required for connecting the signal. The Autobalance signal input and the Busy signal output are used in the DC Strain Module.
- The alarm signals are output on the terminal block attached to the main module as standard accessory
- It is available on the Logic/Pulse module. \*5 Method of detection

Volt./Temp. module: The alarm is detected in the sampling interval when the sampling interval is shorter than 5 seconds. The alarm is detected every 5 seconds when the sampling interval

is longer than 5 seconds.

Other modules: The alarm is detected every 1ms when the sampling interval is shorter than 1ms. The alarm is detected in the sampling interval when the sampling interval is set between 2ms to 5 seconds. The alarm is detected every 5 seconds when the sampling interval is

- \*6. It is available when the captured data is saved to the built-in RAM. The pre-trigger function may not work
- in combination with the trigger settings.

  The result of real time calculation is displayed in the digital display mode.
- \*8. When the captured data destination is set to the built-in-RAM, the captured data is not maintained after a power failure. The built-in Flash or the SD memory card may be damaged by a power failure if it is being accessed to write data. If the memory device is not damaged, the closed data file is maintained.
- The file is closed every one minute while data is being captured.

  The use driver mode is started by setting of the switch on the main module. It can be also started when the power is turned on while pressing the key on the display module.
- 10. The SD memory card is not included as a standard accessory. The SSD module is an option.
  11. The capacity for saving the data is set to one third of available memory when the captured data destination is set to a device other than the built-in-RAM. The sampling speed is limited up to
- \*12. The Sync cable (B559) is required when this function is used. The GL-Connection software is required when the synchronizing function is used.
- \*13. The SP2 or higher service pack need to be installed.
  \*14. The captured data that is saved to the built-in-RAM or SSD cannot be saved to the PC in real time. The data in the built-in-RAM or SSD needs to be transferred to the PC after data capture is complete.
- \*15. Most operations can be selected by both the touch panel and keys.
  \*16. When the display module is mounted at an angle using the bracket, the display module is connected to the main module by a LAN cable that is attached to the display module as a standard accessory
- \*17. The sampling speed in the CL 7000 is limited to the fastest sampling speed of attached signal conditioning module. When the specified sampling speed is faster than the module, the sampling is done in fastest sampling on the module. The same value is stored to the memory device in the specified sampling speed until data is renewed by the next sampling.

Brand names and product names listed in this brochure are the trademarks or registered trademarks of their respective owners. Specifications are subject to change without notice.



# **GRAPHTEC**

Graphtec Corporation

503-10 Shinano-cho, Totsuka-ku, Yokohama 244-8503, Japan Tel: +81-45-825-6250 Fax: +81-45-825-6396 Email: webinfo@graphtec.co.jp

Website http://www.graphteccorp.com



**GRAPHTEC Modular Type Data Acquisition Unit DATA PLATFORM** GL7000

To measure the selected signal on demand with the selected number of channels and time interval



www.graphteccorp.com

# The new generation data acquisition unit

It can measure the desired signal according to the needs and can expand into other applications adding different amplifier modules. It can be attached to a display module having a touch panel, used as a stand-alone unit or embedding into a system.





Main module

The number of channels and measurement types

Attaching the high-definition display module with touch panel

to different locations for remote operation by connecting it to the main module with a LAN cable\*, it also can be embedded into the system.

Measurement settings and signal measurement can both be done without a PC by attaching the display module. The display module can be moved

parameter settings

allows stand-alone operation or embedding into a system

The detachable display module allows both stand-alone and embedded system configurations

The module can still be operated by the PC even when the display module is connected.

Support interface friendly with the PC

Ethernet (10BASE-T, 100BASE-TX) and USB2.0 (Hi-speed) interface are standard.

and accessing the captured data in memory devices such as the built-in memory. SD card\* and SSD

\* SD memory card is not included as standard accessory. SSD module is an option

Each interface port is located in the front of the unit for easy cable connnection.

Improved ease-of-use with the high-definition display

The touch panel makes setting the conditions intuitive, and it can

also be operated using the cursor keys similar to the GL series.

can be added to the amplifier module



Module is fixed by a screw



\* Up to 10m using CAT5 LAN cable (straight connection

Intuitive operation is increased by the touch panel


# The amplifier module can be expanded to accommodate a wide variety of measurements

## A wide variety of measurements can be supported by the amplifier module

Measurments for different applications can be added to the amplifier module. It is also possible to mix measurements by adding different types of modules.

## Maintains sampling speed even if the number of amplier modules are increased

Voltage\* and Volt/Temp amplifier can maintain high-speed and multichannel measurments without dropping the sampling speed. even if the number of modules are increased.



## Amplifier can be attached to up to 10 modules

Up to 10 amplifier modules can be attached for multi-channel measurments, with up to 112 channels on one GL7000.



Amplifier	Channels	Max. sampling	Media type	Max. sampling speed in the GL7000				
Module	in 1 module	speed in the module	to save data	Attached to 1 or 2 modules	Attached to 3 or 4 modules	Attached to 5 to 10 modules		
			Built-in RAM		10/2/1104400 1 0/0/1104400			
Voltage	10 ch	1 k Samples/s	Built-in Flash		1 k Samples/s (1ms interval)			
Module	10 (11	(1ms interval)	SD card					
			SSD *3	1				
			Built-in RAM					
Volt./Temp.	10 ch	100 Samples/s	Built-in Flash	100 Samples/s				
Module	10 (11	(10ms interval)	SD card	(10ms interval)				
			SSD *3					
	4 ch	1 M Samples/s	Built-in RAM		1 M Samples/s (1µs interval)			
High-speed			Built-in Flash	1 k Samples/s (1ms interval)				
voltage Module	4 CII	(1µs interval)	SD card	i k Salliples/s (Tills lillerval)				
Module			SSD *3	1 M S/s (1µs interval)	500 k S/s (2us interval)	200 k S/s (5µs inte		
		In Logic mode,	Built-in RAM		1 M Samples/s (1µs inter	rval) *1		
			Built-in Flash	1 k Samples/s (1ms interval) *1				
		1 M Samples/s	SD card					
Logic	16 ch	(1µs interval)	SSD *3	1 M S/s (1µs interval)	500 k S/s (2us interval) 200k S/s (5us interval)			
/Pulse	10 (11	In Dulas made	Built-in RAM	1 M S/s (1µs interval)	interval)			
Module		In Pulse mode, 10 k Samples/s (100µs interval)	Built-in Flash	Built-in Flash SD card 1 k S/s (1ms interval)				
			SD card					
			SSD *3	1 M S/s (1µs interval)				

## Multi-channel measurement is possible to 1120 channels using the PC

Up to 10 units of the GL7000 can be connected to 1 PC through LAN or USB and controlled using the software.

Up to 5 units of the GL7000 can be fully synchronized using the sync. cable

The start/stop trigger, and sampling can be synchronize in the GL7000 when they are connected by a sync cable.  $\P$ The master and slave units are automatically identified. Sync OUT Sync IN

\*3: SSD module is an option. Number of channels for pulse input will be limited when the High-speed voltage module and

# Up to 112ch on one GL7000. Up to 1120ch total

## FTP client function

and touch panel

Captured data is periodically transferred to the FTP server for backup

## DHCP client function The IP address of the GL7000 is automatically obtained from the DHCP server

## It can be controlled by using a WEB browser such as Internet Explorer. It also supports monitoring the signal, GL7000 can emulate an external USB device for quick data file transfer when it is started in the USB drive mode. The file in the built-in Flash or the SD card can be

The clock on the GL7000 is periodically synchronised with the NTP server.

Large easy-to-read 5.7-inch high-definition LCD monitor

Utilises a bright clear 5.7 inch wide TFT color LCD monitor (VGA: 640 x 480 dots)

Makes it easy to read data in wave form or digital form and to check measurment

# Supports four destinations to save the captured data according to the conditions of the measurement

## 1 Built-in RAM

The RAM to save 2 million samples is built into each amplifier module. The data capture duration does not decrease with increasing numbers of channels because the built-in RAM for each amplifier module is used.

## 3 SD memory card

SD card slot (supports SDHC, up to 32GB) is standard on the main module. The captured data can be saved directly to the SD memory card when the sampling is not faster than 1ms (sampling speed: 1 k Samples/s). It supports hot-swap so the SD memory card can be replaced during measurement without data loss. The captured data can be transferred easily to the PC in offline condition.

\* The hot-swap is possible when the sampling is slower than 100ms.

## 2 Built-in Flash memory

The 2GB of Flash memory is built into the main module. The captured data can be saved directly to the built-in Flash memory when the sampling is not faster than 1ms (sampling speed: 1 k Samples/s). Saved data is retained even when power is turned off because flash memory is used.

## 4 SSD module (64GB)

Allows large amounts of data to be quickly saved when the optional SSD module is attached. The captured data can be saved directly to the SSD when the sampling is not faster than 1µs (sampling speed: 1 M Samples/s).\* It has a high vibration resistance and saved data is also

retained even when power is turned off.

## Capturing times -

			Single module attached								10 modules attached																				
Amplifier Module		Device Capacity		Sampling speed (interval)					number (interval)																						
			of ch.	1 M S/s (1µs)	500 k S/s (2µs)	200 k S/s (5µs)	1 k S/s (1ms)	100 S/s (10ms)	1 S/s (1s)	of ch.	1 M S/s (1µs)	500 k S/s (2μs)	200 k S/s (5μs)	1 k S/s (1ms)	100 S/s (10ms)	1 S/s (1s)															
	Built-in RAM	2 M samples					33 min.	5 hrs.	23 days					33 min.	5 hrs.	23 days															
Voltage	Built-in Flash memory	1.87GB		N/A	N/A	N/A	21 hrs.	8 days	893 days	100	NI/A	N/A N/A	N/A	2 hrs.	24 hrs.	103 days															
Module	SD memory card *2	32GB is attached	10	N/A	IVA	N/A	22 hrs.	9 days	956 days	100	N/A			2 hrs.	26 hrs.	111 days															
	SSD*2	64GB						221113.	3 days	330 days					21113.	201113.	111 days														
	Built-in RAM	2 M samples	10		10						5 hrs. 23 days					5 hrs.	23 days														
Volt./Temp	Built-in Flash memory	1.87GB				NI/A	N/A N/A	N/A	N/A	8 days	893 days	100	N/A N/A	NI/A	N/A	N/A	24 hrs.	103 days													
Module	SD memory card *2	32GB is attached				10	IV/A	I IVA	IN/A	IN/A	9 days	9 days 956 days	100	IVA	IVA	IN/A	IN/A	26 hrs.	111 daγs												
	SSD *2	64GB						3 days	See days						201113.	TTT days															
	Built-in RAM	2 M samples		2 sec.	4 sec.	10 sec.	33 min.	5 hrs.	23 days		2 sec.	4 sec.	10 sec.	33 min.	5 hrs.	23 days															
High-speed	Built-in Flash memory	1.87GB																			<b>.</b>	39 hrs.	16 days	1660 days					5 hrs.	53 hrs.	223 days
Voltage Module	SD memory card *2	32GB is attached		4	N/A	N/A	N/A	40.1	17 daγs	1775 days	40	N/A	N/A	N/A	5 hrs	57 hrs.	000 1														
	SSD *2 64GB		134 sec.	268 sec.	671 sec.	42 hrs.	17 days	1770 days				95 sec.	5 hrs.	OTTIIS.	239 days																

<sup>\*2:</sup> The file size of the captured data is limited up to 2GB.

# Software for high performance and easy operation

The GL7000 can be controlled by the GL-Connection software that is included. The software has convenient functions such as saving data to the PC, replaying captured data, and converting data form. It is an integrated application software for the GL series, the GL900, GL820 and GL220 can also be connected.

\*The version for supporting other GL series will be available in December 2012







## Various measurement screens

The measurement signal can be displayed as various types of screens by the unit, the module or the specific channels that are specified in the group function. It can also be displayed as a combination of the capturing data and captured data, the Y-T format and the X-Y format, simultaneously. Up to 112 channels can be displayed in each window.\*









Digital monitor screen (with calculation)

## Multi-window function, measured waveform can be displayed in various forms using multiple windows



The complete measured waveform

Displayed items in each window can be specified by the unit, the module or channels. (ex.: waveform measured in the each unit is displayed in the separate screens.)

## Useful functions For real time and the post processing.

 Statistical . The maximum, minimum, peak, and average values are displayed while capturing data. The value between the cursors of the maximum, minimum peak, average, and RMS will be displayed when replaying captured data.

.. The data can be converted to the CSV format for a specified period, all data, or multiple files. A file can also be created by compressing or consolidating

. The search point can be set by the level, alarm, or time (the beginning of the data,

# center, end, trigger point, the specified time, instruction time, the number specified)

# **Amplifier Module**

# **Amplifier Module**

Module	Voltage	High Speed Voltage	Voltage/Temperature	Logic/Pulse
Model number	GL7-V	GL7-HSV	GL7-M	GL7-L/P
Module image				
Number of input channels	10 channels	4 channels	10 channels	16 channels
Input terminal	Screw terminal (M3)	BNC connector	Screw terminal (M3)	Circular connector (10 position, socket)
Input method	All channels isolated simultaneous samplir		All channels isolated balanced input, scanning channels for sampling	All channels common ground, simultaneous sampling
Sampling speed	1 k Samples/s to 1 Sample/h (1ms to 1hr. interval)	1 M Samples/s to 1 Sample/h (1µs to 1hr. interval)	100 Samples/s with 1-10ch to 1 Sample/h (10ms with 1-10ch to 1hr. interval)	Logic mode: up to 1 M Samples/s (1µs interval) Pulse mode: up to 10 k Samples/s (100µs interval)
Measurement range	100mV to 100V F.S.,	and 1-5V F.S.	Volt.: 20mV to 50V F.S., and 1-5V F.S. Temp.: Thermocouple: K, J, E, T, R, S, B, N, W (WRe5-26) RTD: Pt100 (IEC751), Pt1000 (IEC751), Pt100J (JIS)	Bi-level signal, up to 24V Select either Logic or Pulse mode Logic: Signal pattern Pulse: Counting in Instant, Accumulating, Rotation (max. 15 million count)
A/D converter	Successive Approxim	ation, 16 bits	Sigma-delta, 16 bits	
Maximum Voltage	Between channels: 10 Between inputs and 0	,	Between channels: 350 V, 1 min. Between inputs and GND: 350 V, 1 min.	
Built-in RAM	2 million samples			

# Combinations of amplifier modules

Simple measurement with a single module



ex.: single High Speed Voltage module (4 channels)

Variety of measurements with different amplifier modules



ex.: two Voltage modules (20 ch) and two Volt./Temp. modules (20 ch), total 40 channels

## Multi-channel measurement with several amplifier modules




# Typical applications

UPS (Uninterruptible Power Supply) test

Evaluation testing for the charging current, the output voltage with discharge capacity, etc




- Supports long term measurement with high-speed sampling
   Higher voltage capability
- Expandable with additional modules



## Bearing durability test

Utilized in temperature, vibration and other testing to check the durability of the bearings that are used in extreme temperature and vibration conditions.

- Supports low- to high-speed
- Very large storage
- Expandable with additional modules
- PC compatible



Bearings for cars; Power steering, Engines, Hub Units, Alternators, etc

## Washer-dryer evaluation test

Used to measure various evaluation items such as the temperature, flow rate, air volume, sound, vibration, etc. using multi-type input and low- to high-speed sampling



- Maintaining the sampling speed in the multi-channel Supporting a variety of measurements due to flexible module combinations
- Very large storage



## Vehicles

## Automobile battery test

Utilized to measure the charge and discharge characteristics of the battery in vehicles that have energy saving controls such as idling-stop, etc...



- Supports long term sampling
- Supports reconfiguration to fit the desired measurement
- PC compatible

# Chassis dynamometer test Capturing various data such as the torque, etc by the driving pattern



### Example Others Geothermal test

Used for demonstraton and evaluaton testing of new air conditioning systems that utilize a geothermal heat pump for heat exchange.



 Supports various amplifier modules

Monitoring on PC using

Very large storage



			0 10 11							
Voltage/Temperature Module										
Model numb			GL7-M							
Number of input channels			10 channels							
Input method			All channels isolated balanced input,	rminal (M2 agraus)						
0			Scans channels for sampling, Screw to							
Sampling sp			100 Samples/s with 1-10ch to 1 Sampl							
Measure-	Voltag		20, 50, 100, 200, 500 mV, 1, 2, 5, 10, 2		F.S.					
ment range	Tempe	erature	Thermocouple: K, J, E, T, R, S, B, N, a RTD: Pt100, JPt100(JIS), Pt1000(IEC7							
	Humid	ity *1	0 to 100 % (using scanning function in	5V range, humidity	sensor B-530)					
Measure-	Voltag	е	± 0.1 % of F.S.							
ment accuracy*2		Thermo- couple	Measurement range Measurement accuracy							
		R/S	0 °C ≤ TS ≤ 100 °C	± 5.2 °C						
			100 °C < TS ≤ 300 °C	± 3.0 °C						
			R: 300 °C < TS ≤ 1600 °C	± (0.05 % of reading	in + 2 0 °C)					
			S: 300 °C < TS ≤ 1760 °C	± (0.05 % of reading						
		В	400 °C ≤ TS ≤ 600 °C	± 3.5 °C	ig · 2.0 0)					
		Ь			- 1 2 0 °C)					
		IZ.	600 °C < TS ≤ 1820 °C	± (0.05 % of readin						
		K	-200 °C ≤ TS ≤ -100 °C	± (0.05 % of readin						
		_	-100 °C < TS ≤ 1370 °C	± (0.05 % of readin						
		E	-200 °C ≤ TS ≤ -100 °C	± (0.05 % of readin						
		_	-100 °C < TS ≤ 800 °C	± (0.05 % of readin						
		T	-200 °C ≤ TS ≤ -100 °C	± (0.1 % of reading						
			-100 °C < TS ≤ 400 °C	± (0.1 % of reading	( + 0.5 °C)					
		J	-200 °C ≤ TS ≤ -100 °C	± 2.7 °C						
			-100 °C < TS ≤ 100 °C	± 1.7 °C ± (0.05 % of reading + 1.0 °C)						
			100 °C < TS ≤ 1100 °C							
		N	0 °C ≤ TS ≤ 1300 °C	± (0.1 % of reading	ı + 1.0 °C)					
		RTD	0 °C ≤ TS ≤ 2000 °C ± (0.1 % of reading + 1.5 °C)							
			Reference Junction Compensation (R.J.C.) accuracy: ± 0.5 °C *3							
			Measurement range	Driving current	Accuracy					
		Pt100	-200 °C to 850 °C (FS = 1050 °C)	1 mA	± 1.0 °C					
		JPt100	-200 °C to 500 °C (FS = 700 °C)	1 mA	± 0.8 °C					
		Pt1000	-200 °C to 500 °C (FS = 700 °C)	0.2 mA	± 0.8 °C					
R.J. Comper	nsation		Selecting of the internal or external							
A/D Convert			Sigma-Delta type, 16 bits (effective reso	olution: 1/40000 of m	easuring full range)					
Stability with			0.01 % of F.S./°C							
temperature		1	0.02 % of F.S./°C							
Input impeda		*	1 MΩ ± 5 %							
Maximum	Between (+) / (-) terminal Between channels		60 V p.p.							
iriput voitage			60 V p-p							
	Between channel / GND		60 V p-p							
Maximum voltage	Betwe	en	350 V p-p (1 minute)							
voltage	Channels Between channel / GND		350 V p-p (1 minute)							
Isolation	Between input /	en	Min. 50 MΩ (at 500 V DC)							
Common-mode rejection ratio			Min. 90 dB (50/60 Hz, Signal source impedance: Max. 300 Ω)							
	ac rejet	Juoniado	Off, 2, 5, 10, 20, 40 (Moving average in							
Filter			longer than 5 seconds, the data sample							
			be used for creating the average value		c (5 seconds) Will					
5) /t				•						
5V output	-	044 D	Driving the humidity sensor B-530, 1 cl							
External dime	ensions	(W×D×H)		1011)						
Weight			Approx. 770 g							
Notes;				#4 It is affa - P						

Voltage mod	lule specifications	Voltage	High Speed Voltage			
Model numb	er	GL7-V	GL7-HSV			
Number of it	nput channels	10 channels 4 channels				
Input metho	d	All channels isolated unbalanced input, Simultaneous sampling, Screw terminal Simultaneous sampling, BNC con				
	eed (interval)	1 k Samples/s to 1 Sample/h (1ms to 1h)				
Measureme	nt range	100, 200, 500 m V . 1, 2, 5, 10, 20, 50,	100 V, and 1-5 V/F.S.			
Measureme	nt accuracy*5	± 0.25 % of F.S.				
A/D Conver	ter	Successive Approximation type, 16 bit (effective resolution: 1/40000 of measu				
Stability with		0.01 % of F.S./°C				
temperature	Zero	0.02 % of F.S./°C				
Input imped		1 MΩ ± 5 %				
Maximum input	Between (+) / (-) terminal	100mV to 1V range: 60 V p-p, 2V to 100V range: 100 V p-p				
voltage	Between channels	60 V p-p				
	Between channel / GND	60 V p-p				
Maximum voltage	Between channels	1000 V p-p (1 minute)				
	Between channel / GND	1000 V p-p (1 minute)				
Isolation	Between input / GND	Min. 50 MΩ (at 500 V DC)				
Common-mode rejection ratio		Min. 90 dB (50/60 Hz, Signal source impedance: Max. 300 Ω)				
Frequency r	esponse	DC to 1 k Hz (at +1/-3 dB)	DC to 2 k Hz (at +1/-3 dB)			
Filter (Low pass)		Off, Line(1.5Hz), 5, 50, 500 Hz (-3dB, 6db/oct) Off, Line(1.5Hz), 5, 50, 500, 5k, 50k Hz (-3dB, 6dB/oct)				
External dime	ensions (W×D×H)	49 x 136 x 160 mm (Excluding protrusion)				
Weight		Approx. 840 g Approx. 740 g				

Rotation count (RPM)  Range 50, 500, 500, 50 k, 500 k, 50 M, 50 M, 50 M counts/F.S.  Accumulating Function Accumulating the number of pulses per sampling interval and then it is converted to RPM  Range 50, 500, 50 k, 500 k, 50 M, 50 M, 50 M, 50 M rpm/F.S.  Accumulating the number of pulses from the start of measurement count Range 50, 500, 5 k, 50 k, 50 M, 50 M, 50 M, 50 M, 50 M counts/F.S.  Instant count Function Counting the number of pulses per sampling interval (count is reset at each sampling)  Range 50, 500, 5 k, 50 k, 50 k, 50 M, 50 M, 50 M counts/F.S.  Max. input frequency 1 M Hz  Max. number of count 15 M counts (24 bits counter is used)  Voltage range 10 to +24 V (common ground)  Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 2.5 V Hysteresis Approx. 0.5 V (2.5 V to 3 V)						
Number of input channels Input method Input						
Input method  All channels common ground, simultaneous sampling, Circular connector (4ch/connector)  Sampling speed  Logic mode Pulse mode Up to 1 M Samples/s (1us interval) Pulse mode Up to 1 N Samples/s (100µs interval)  Measurement mode Selecting of the Logic input mode or Pulse input mode *6  Rotation count (RPM), Accumulating count, Instant count  Function Counting the number of pulses per sampling interval and then it is converted to RPM  Range 50, 500, 500, 50 K, 500 K, 50, 50 M, 50 M, 50 M ounts/F.S.  Accumulating function Counting the number of pulses from the start of measurement count  Range 50, 500, 5 K, 50 K, 500 K, 5 M, 50 M, 50 M counts/F.S.  Instant count Counting the number of pulses per sampling interval count is reset at each sampling)  Range 50, 500, 5 K, 50 K, 500 K, 5 M, 50 M, 500 M counts/F.S.  Max. input frequency 15 M ocunts (24 bits counter is used)  Voltage range Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 2.5 V Hysteresis Approx. 0.5 V (2.5 V to 3 V)	Model numb	er	GL7-L/P			
Sampling speed Pulse mode Up to 1 M Samples/s (1µs interval) Measurement mode Selecting of the Logic input mode or Pulse input mode *6 Mode Pulse Rotation count (RPM). Accumulating count, Instant count Rotation count (RPM) Range 50, 500, 500, 50 k, 50 k, 50 M, 50 M, 50 M m pm/F.S. Accumulating Function Accumulating the number of pulses from the start of measurement count Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S. Instant Function Counting the number of pulses per sampling interval and then it is converted to RPM Range 50, 500, 500, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S. Instant Function Counting the number of pulses per sampling interval (count is reset at each sampling) Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 50 M counts/F.S. Max. input frequency 1 M Hz Max. number of count 15 M counts (24 bits counter is used) Input signal Voltage range 0 to ±24 V (common ground) Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 0.5 V (2.5 V to 3 V)	Number of in	put channels				
Sampling speed Pulse mode Up to 1 M Samples/s (1µs interval) Measurement mode Selecting of the Logic input mode or Pulse input mode *6 Mode Pulse Rotation count (RPM). Accumulating count, Instant count Rotation count (RPM) Range 50, 500, 500, 50 k, 50 k, 50 M, 50 M, 50 M m pm/F.S. Accumulating Function Accumulating the number of pulses from the start of measurement count Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S. Instant Function Counting the number of pulses per sampling interval and then it is converted to RPM Range 50, 500, 500, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S. Instant Function Counting the number of pulses per sampling interval (count is reset at each sampling) Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 50 M counts/F.S. Max. input frequency 1 M Hz Max. number of count 15 M counts (24 bits counter is used) Input signal Voltage range 0 to ±24 V (common ground) Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 0.5 V (2.5 V to 3 V)	Input method	t	All channels common ground, simultaneous sampling,			
Pulse mode   Up to 10 k Samples/s (100µs interval)			Circular connector (4cn/connector)			
Measurement mode Selecting of the Logic input mode or Pulse input mode *6  Mode Pulse Rotation count (RPM), Accumulating count, Instant count  Counting the number of pulses per sampling interval and then it is converted to RPM  Range 50, 500, 500, 50 k, 50 k, 50 M, 50 M, 50 M, 500 M rpm/F.S.  Accumulating Function Accumulating the number of pulses from the start of measurement count  Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S.  Instant Function Counting the number of pulses per sampling interval (count is reset at each sampling)  Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S.  Counting the number of pulses per sampling interval (count is reset at each sampling)  Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 50 M counts/F.S.  Max. input frequency 1 M Hz  Max. number of count 15 M counts (24 bits counter is used)  Input signal Voltage range 10 to +24 V (common ground)  Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 2.5 V Hysteresis Approx. 0.5 V (2.5 V to 3 V)			Up to 1 M Samples/s (1µs interval)			
Mode         Pulse         Rotation count (RPM), Accumulating count, Instant count           Rotation count (RPM)         Function         Counting the number of pulses per sampling interval and then it is converted to RPM           Range         50, 500, 500, 50 k, 500 k, 5 M, 50 M, 50 M, 50 M mm/s.S.           Accumulating function count         Accumulating the number of pulses from the start of measurement count           Range         50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S.           Instant count         Counting the number of pulses per sampling interval (count is reset at each sampling)           Range         50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 50 M, 50 M counts/F.S.           Max. input frequency         1 M Hz           Max. number of count         15 M counts (24 bits counter is used)           Input signal         Voltage range           Signal type         Contact (Relay), Open collector, Voltage           Threshold         Approx. 2.5 V           Hysteresis         Approx. 0.5 V (2.5 V to 3 V)	speed	Pulse mode	Up to 10 k Samples/s (100µs interval)			
Rotation count (RPM)  Range 50, 500, 500, 50 k, 500 k, 50 M, 50 M, 50 M counts/F.S.  Accumulating Function Accumulating the number of pulses per sampling interval and then it is converted to RPM  Range 50, 500, 50 k, 500 k, 50 M, 50 M, 50 M, 50 M rpm/F.S.  Accumulating the number of pulses from the start of measurement count Range 50, 500, 5 k, 50 k, 50 M, 50 M, 50 M, 50 M, 50 M counts/F.S.  Instant count Function Counting the number of pulses per sampling interval (count is reset at each sampling)  Range 50, 500, 5 k, 50 k, 50 k, 50 M, 50 M, 50 M counts/F.S.  Max. input frequency 1 M Hz  Max. number of count 15 M counts (24 bits counter is used)  Voltage range 10 to +24 V (common ground)  Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 2.5 V Hysteresis Approx. 0.5 V (2.5 V to 3 V)	Measuremen	t mode	Selecting of the Logic input mode or Pulse input mode *6			
count (RPM)  Range 50, 500, 500, 50 k, 50 k, 50 M, 50 M, 50 M rpm/F.S.  Accumulating Function Accumulating the number of pulses from the start of measurement count  Range 50, 500, 5 k, 50 k, 50 k, 50 M, 50 M, 50 M counts/F.S.  Instant count Function Counting the number of pulses per sampling interval (count is reset at each sampling)  Range 50, 500, 5 k, 50 k, 50 k, 50 M, 50 M, 50 M counts/F.S.  Max. input frequency 1 M Hz  Max. number of count 15 M counts (24 bits counter is used)  Input signal Voltage range Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 2.5 V Hysteresis Aprox. 0.5 V (2.5 V to 3 V)	Mode	Pulse	Rotation count (RPM), Accumulating count, Instant count			
Accumulating Function Accumulating the number of pulses from the start of measurement count  Range 50, 500, 5 k, 50 k, 50 k, 50 M, 50 M, 50 M, 50 M counts/F.S.  Instant count Counting the number of pulses per sampling interval (count is reset at each sampling)  Range 50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S.  Max. input frequency 1 M Hz  Max. number of count 15 M counts (24 bits counter is used)  Voltage range 0 to +24 V (common ground)  Signal type Contact (Relay), Open collector, Voltage  Threshold Approx. 2.5 V  Hysteresis Approx. 0.5 V (2.5 V to 3 V)	Rotation count (RPM)					
count Range 50, 500, 5 k, 50 k, 50 k, 50 M, 50 M, 50 M counts/F.S.  Instant count Function Counting the number of pulses per sampling interval (count is reset at each sampling) Range 50, 500, 5 k, 50 k, 50 k, 50 M, 50 M, 50 M counts/F.S.  Max. input frequency 1 M Hz Max. number of count 15 M counts (24 bits counter is used) Input signal Voltage range Signal type Contact (Relay), Open collector, Voltage Threshold Approx. 2.5 V Hysteresis Approx. 0.5 V (2.5 V to 3 V)		Range	50, 500, 5000, 50 k, 500 k, 5 M, 50 M, 500 M rpm/F.S.			
Instant count  Function  Counting the number of pulses per sampling interval (count is reset at each sampling)  Range  50, 500, 5 k, 50 k, 50 k, 50 k, 50 M, 50 M, 50 M counts/F.S.  Max. input frequency  1 M Hz  Max. number of count  15 M counts (24 bits counter is used)  Voltage range  10 to +24 V (common ground)  Signal type  Contact (Relay), Open collector, Voltage  Threshold  Approx. 2.5 V  Hysteresis  Approx. 0.5 V (2.5 V to 3 V)	Accumulating count	Function	Accumulating the number of pulses from the start of measurement			
Count is reset at each sampling		Range	50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S.			
Max. input frequency         1 M Hz           Max. number of count         15 M counts (24 bits counter is used)           Input signal         Voltage range         0 to +24 V (common ground)           Signal type         Contact (Relay), Open collector, Voltage           Threshold         Approx. 2.5 V           Hysteresis         Approx. 0.5 V (2.5 V to 3 V)		Function	Counting the number of pulses per sampling interval (count is reset at each sampling)			
Max. input frequency         1 M Hz           Max. number of count         15 M counts (24 bits counter is used)           Input signal Signal type         0 to +24 V (common ground)           Signal type         Contact (Relay), Open collector, Voltage           Threshold         Approx. 2.5 V           Hysteresis         Approx. 0.5 V (2.5 V to 3 V)		Range	50, 500, 5 k, 50 k, 500 k, 5 M, 50 M, 500 M counts/F.S.			
Input signal   Voltage range   0 to +24 V (common ground)	Max. input fro	equency				
Signal type         Contact (Relay), Open collector, Voltage           Threshold         Approx. 2.5 V           Hysteresis         Approx. 0.5 V (2.5 V to 3 V)	Max. number	of count	15 M counts (24 bits counter is used)			
Threshold	Input signal	Voltage range	0 to +24 V (common ground)			
Hysteresis Approx. 0.5 V (2.5 V to 3 V)		Signal type	Contact (Relay), Open collector, Voltage			
,		Threshold	Approx. 2.5 V			
		Hysteresis	Approx. 0.5 V (2.5 V to 3 V)			
Filter   Off or On (-3 dB at 50 Hz)	Filter		Off or On (-3 dB at 50 Hz)			
External dimensions (W×D×H) 49 x 136 x 160 mm (Excluding protrusion)	External dime	ensions (W×D×H)	49 x 136 x 160 mm (Excluding protrusion)			
Weight Approx. 700 g	Weight		Approx. 700 g			

- \*1. Using optional humidity sensor (B-530).
- \*1. Using optional numidity sensor (B-530).

  \*2. Subject to the following conditions;

  \*Room Temperature is 23°C ±5°C.

  \*When 30 minutes or more have elapsed after power was turned on.

  \*Filter is set to 10.

  \*Sampling rate is set to 1s with 10 channels.


  \*GND terminal is connected to ground.

  \*3. Wire size of thermocouple to use is 0.32mm in T type,

  0.65mp in other two-

- 0.65mm in other type.
- \*4. It is effective when the 10, 20, 50ms sampling is used. When the sampling is slower than 100ms, it is not effective by executing the Zero calibration periodically.
- \*5. Subject to the following conditions:
- Subject to the following conditions;
   Room Temperature is 23°C ±5°C.
   When 30 minutes or more have elapsed after power was turned on.
   Filter is set to Line (1.5 Hz).
   Sampling rate is set to 1s.
   GND terminal is connected to ground.

\*6. The measureing mode is set in each module (16 channels). When the module is used in the Logic, up to 7 modules can be attached to one main module. (max. 112 ch) When the module is used in the Pulse, up to 2 modules can be attached to one main module. (max. 32 ch) The amplifier module can be attached to up to 10 modules. The maximum number of channels is limited to up to 112 channels.



Brand names and product names listed in this brochure are the trademarks or registered trademarks of their respective owners. Specifications are subject to change without notice.



# **GRAPHTEC**

**Graphtec Corporation** 

503-10 Shinano-cho, Totsuka-ku, Yokohama 244-8503, Japan Tel: +81-45-825-6250 Fax: +81-45-825-6396

Email: webinfo@graphtec.co.jp

